

Front wheel



Mid wheel

Rear wheel

Power Wheelchairs

Independence in motion.



Paediatric Series	Koala	K300 PS Jr.	M300 PS Jr.	K450 MX
Max user weight	35 kg	75 kg	75 kg	60 kg
Max speed	6.5 km/h	8 km/h 10 km/h	10 km/h	8 km/h
Range	24 km*	25 km*	20 km*	27 km*
Base width	23"	24"	24"	25"
Base length	32"	40"	36.5"	35"
Min turning radius	21"	25"	20"	28"
Ground clearance	2.5"	3"	3"	2.5"
Weight w/ batteries	102 kg (M40)	123 kg (Gr 34)	142 kg (Gr 34) 151 kg (Gr 24)	153 kg (Gr 34)
Seat-to-floor height	15" Elevator	16.5" Elevator 16.5", 17.25", 18.5" Fixed	17" Elevator 17", 17.75", 18.5" Fixed	3" – 26" Elevator
Seat elevator	8"	Optional 8"	Optional 8"	Optional 8"
Power tilt options	0° – 25° Power	0° – 45° Manual or Power	0° – 45° Manual or Power	0° – 45° Power
Recline options	85° – 120° Manual	85° – 120° Manual	85° – 120° Manual	85° – 105° Manual
Legrest options	90° – 150° Manual	70° or 90° Swing-Away 90° – 150° Centre Mount	70° Swing-Away 90 – 150° Centre Mount	90° – 125° Manual
Seat depth	10", 12", 14"	10" – 18"	10" – 18"	10" – 18" (by 1" incr.)
Seat width	10", 12", 14"	11" – 16" (by 1" incr.)	11" – 16" (by 1" incr.)	10", 12", 14", 16"
Backrest height	14", 16", 20"	16.5" – 22.5" (by 1" incr.)	16.5" – 22.5" (by 1" incr.)	14", 16", 20" (MX) 16.5" – 22.5" (PS Jr)

All specifications may vary based upon configuration. | Chair weights are approximate and include base, batteries, power seat functions and seating system without accessories. | *Actual driving range will vary based on driving and battery conditions.

Front wheel

Mid wheel

Rear wheel



Rehab Series	F3 Corpus	F5 Corpus	F5 Corpus VS	M1	M3 Corpus	M5 Corpus	M300 HD	X850
Max user weight	136 kg	136 kg	136 kg	136 kg	136 kg	136 kg	204 kg	136 kg
Max speed	8 km/h 10 km/h	10 km/h	10 km/h	8 km/h	10 km/h	10 km/h	8 km/h	10 km/h 15 km/h ¹
Range	32.2 km*	32.2 km*	32.2 km*	25.8 km*	32.2 km*	32.2 km*	32.2 km*	45 km*
Base width	24"	25.5"	25.5"	24"	24"	25"	26"	28"
Base length	40" with anti-tips 36" without anti-tips	42" with anti-tips 38" without anti-tips	43"	35.5"	35.5"	37.5"	38"	49.5" – 57.5"
Min turning radius	26.5"	30"	30"	20.5"	20.5"	21.5"	22"	66"
Ground clearance	3"	3"	3"	3"	3"	3"	3"	3.2"
Weight w/ batteries	175 kg (Gr 34) 184 kg (Gr 24)	186 kg (Gr 24)	190 kg (Gr 24)	145 kg (Gr 34)	175 kg (Gr 34) 184 kg (Gr 24)	192 kg (Gr 24)	193 kg (Gr 34) 202 kg (Gr 24)	203 kg (M31)
Seat-to-floor height	17.5", 18.5", 19.5"	17.5", 18.5", 19.5"	17.5", 18.5", 19.5"	16", 17", 18"	17.5", 18.5", 19.5"	17.5", 18.5", 19.5"	18", 19", 20"	21"
Seat elevator	Optional 12"	Optional 14"	14"	—	Optional 12"	Optional 14"	Optional 8"	Optional 8"
Power tilt options	0° – 50° Posterior 5°, 10°, 20° & 30° Anterior	0° – 50° Posterior 5°, 10°, 20° & 45° Anterior	0° – 50° Posterior	0° – 50° Posterior	0° – 50° Posterior 5°, 10° & 20° Anterior	0° – 50° Posterior 5°, 10° & 20° Anterior	0° – 45° Posterior	0° – 15° Posterior
Recline options	85° – 120° Manual 85° – 180° Power	85° – 120° Manual 85° – 180° Power	85° – 180° Power	—	85° – 120° Manual 85° – 180° Power	85° – 120° Manual 85° – 180° Power	85° – 120° Manual 85° – 150° Power	90° – 130° Manual 90° – 120° Power
Legrest options	85° – 180° Manual or Power	85° – 180° Manual or Power	90° – 180° Power	80° – 135° Manual 65° – 80° Adjust. Swing-Away	85° – 180° Manual or Power	85° – 180° Manual or Power	85° – 180° Manual or Power	110° – 160° Manual
Seat depth	14" – 22" (by 1" incr.)	14" – 22" (by 1" incr.)	14" – 22" (by 1" incr.)	14" – 22" (by 1" incr.)	14" – 22" (by 1" incr.)	14" – 22" (by 1" incr.)	19" – 25" (by 1" incr.)	14" – 22" (by 1" incr.)
Seat width	17", 19", 21", 23"	17", 19", 21", 23"	17", 19", 21", 23"	14" – 22" (by 2" incr.)	17", 19", 21", 23"	17", 19", 21", 23"	19", 21", 23", 25"	17", 19", 21", 23"
Backrest height	20", 23" – 28" (by 1" incr.)	20", 23" – 28" (by 1" incr.)	23" – 28" (by 1" incr.)	18" – 29"	20", 23" – 28" (by 1" incr.)	20", 23" – 28" (by 1" incr.)	21", 24" – 29" (by 1" incr.)	20", 23" – 28" (by 1" incr.)

All specifications may vary based upon configuration. | Chair weights are approximate and include base, batteries, power seat functions and seating system without accessories. | *Actual driving range will vary based on driving and battery conditions. | ¹15 km/h model only available for use on private property.